



BG12G122 Braid Kit

By Burndy
Catalog # BG12G122

Braid Kit



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

Specifications

Standards - Industry Standards	UL467
Met	
Industry Standard(s)	UL467
Certification - CSA Approved	Yes

Configuration

Connector Type	Braid
----------------	-------

Dimensions

Package Height	0.000 in
Length	12 in
Package Weight	0.000 lb.
Dimension - Width inch	1.63 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	305 mm
Weight	2.022 lb.
Height	0.25 in
Width	1.63 in
Dimension - Length Overall inch	12 in
Dimensions	12 in x 1.63 in x 0.25 in

General

UPC	621945449787
Material	Copper
UPC 12 Digit	621945449787
UPC 14 Digit GTIN	00621945449787

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1680
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)