



# BG12N2U BG Type Braid, 12" Undrilled

By Burndy  
Catalog # BG12N2U

BG Type Braid, 12" Undrilled



## Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](http://www.hubbell.com/config/BRAID) for our Braid Configurator Tool:

## Specifications

Certification - CSA Approved      Yes

## Dimensions

Length      12 in

## General

UPC      621945485181

## Logistics

Minimum Pack Quantity      1  
Carton Quantity      5  
Pallet Quantity      450

## Product Assets

[Catalog \[English\]](#)



A Hubbell brand