



BG12T716 Flexible Copper Braid

By Burndy
Catalog # BG12T716

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	Yes

Configuration

Connector Type	Braid
----------------	-------

Dimensions

Package Height	0.000 in
Length	12 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

General

UPC	781810675199
Material	Copper
UPC 12 Digit	781810675199
UPC 14 Digit GTIN	00781810675199

Logistics

Minimum Pack Quantity	1
Pallet Quantity	4200
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)