



BG18 Flexible Copper Braid, 18 in L

By Burndy
Catalog # BG18

Flexible Copper Braid, 18 in L



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](http://www.hubbell.com/config/BRAID) for our Braid Configurator Tool:

Application

Flexible copper braid jumpers designed to take up linear expansion and contraction

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	No

Configuration

Connector Type	Braid
----------------	-------

Current

Rating - Indoor Amperage	415 A
Rating - Outdoor Amperage	495 A

Dimensions

Dimension - Pad Width inch	1.50 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	457 mm
Dimension - Hole Size inch	0.44 in
Length	18 in
Dimension - D inch	3.00 in
Dimension - N inch	0.75 in
Dimension - Length Overall inch	18.00 in

General

Material - Ferrules	Y
Insulation	Y
Plated	Y
Physical Attribute - Number of Braids	1
Sub Brand	BRAID
UPC	781810005156
Type	B, Flexible
Material	Copper
UPC 12 Digit	781810005156
UPC 14 Digit GTIN	00781810005156

Logistics

Pallet Quantity	780
Carton Quantity	12

Product Assets

[Catalog \[English\]](#)