



BG4D75G120 Braid Kit

By Burndy
Catalog # BG4D75G120

Braid Kit



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](http://www.hubbell.com/config/BRAID) for our Braid Configurator Tool:

Specifications

Standards - Industry Standards	UL467
Met	
Standards - RoHS Compliance	CM
Status	
Industry Standard(s)	UL467
Certification - CSA Approved	Yes

Configuration

Connector Type	Braid
----------------	-------

Dimensions

Package Height	0.000 in
Length	4.75 in
Package Weight	0.000 lb.
Dimension - Width inch	1.5 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	121 mm
Weight	0.116 lb.
Height	0.25 in
Width	1.5 in
Dimension - Length Overall inch	4.75 in
Dimensions	4.75 in x 1.5 in x 0.25 in

General

UPC	621945437623
Material	Copper
UPC 12 Digit	621945437623
UPC 14 Digit GTIN	00621945437623

Logistics

Minimum Pack Quantity	1
Pallet Quantity	3600
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)