



BGBL4, Aluminum Lay-in Lug, 4-14 AWG, #10 Stud

By Burndy
Catalog # BGBL4



Tin Plated Aluminum Lay-in Lug, 4-14 AWG, 1/4" Zinc Plated Terminal Screw, #10 Stud

Features

- UL486B Listed, AL9CU Rated for copper and aluminum conductor combinations up to 90°C
- UL Recognized for grounding and bonding
- Lay-in feature eases installation

Application

For Copper And Aluminum Conductor Combinations Up To 90 DEG C

Specifications

EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-B
Standards - Industry Standards Met	UL 486A-B
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - AL Str Size	• 8 AWG • 6 AWG • 4 AWG
Conductor - AL Str Size Range	8 AWG-4 AWG
Conductor - Copper Str Size	• 14 AWG • 12 AWG • 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG
Conductor - Copper Solid Size	• 14 AWG • 13 AWG • 12 AWG • 11 AWG • 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG

Conductor - Copper Solid Size Range	14 AWG-4 AWG
Conductor Type	• AL C Str-Size • CU C Str-Size • CU C Solid-Size
Conductor - Copper Str Size Range	14 AWG - 4 AWG

Dimensions

Dimension - Pad Width inch	0.38 in
Package Height	0.000 in
Dimension - Height mm	19.8 mm
Dimension - Height inch	0.78 in
Dimension - Height fraction	7/9 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	27 mm
Dimension - Hole Size mm	6 mm
Dimension - Hole Size inch	0.22 in
Dimension - D inch	0.62 in
Dimension - N inch	0.19 in
Dimension - Length Overall inch	1.07 in
Hex Size	Slot

Force Related

Installation Torque Recommended in-lb	35 LBS/in
---------------------------------------	-----------

General

Trade Name	QIKLUG™
Material Type - Screw	Steel - Zinc Plated
Physical Attribute - Screw Type Plated	Slot Y
Sub Brand	QIKLUG
UPC	781810124857
Type	BGBL, Lay-In
Material	Aluminum
Plating Type	Tin
UPC 12 Digit	781810124857
UPC 14 Digit GTIN	00781810124857

Logistics

Pallet Quantity 1
Carton Quantity 1400

Temperature Rating 194

Product Assets

Operational

[Catalog \[English\]](#)



A Hubbell brand