



BIBD2/012, 2-Sided, 12-Cond., Clear Ins.

By Burndy

Catalog # [BIBD2/012](#)

#14 - 2/0 AWG, 12 Ports, Double-sided Entry, Al/Cu Rated, Clear
Plastisol allows visual confirmation conductor is properly inserted



Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - AL Str Size	• 8 AWG • 6 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG
Conductor - AL Str Size Range	8 AWG-2/0 AWG
Conductor - Copper Str Size	• 14 AWG • 12 AWG • 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG

Conductor Size	• 1 AWG • 1/0 • 2/0 Str
Conductor Type	14-2/0 AWG • AL C Str-Size • CU C Str-Size
Conductor - Copper Str Size Range	14 AWG - 2/0 AWG

Configuration

Physical Attribute - Number of Screws	12
Number Of Ports	12
Connector Type	Multi Tap

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Height	0.000 in
Dimension - Height mm	35.1 mm
Dimension - Height inch	1.38 in
Dimension - Height fraction	1.375 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	209 mm
Dimension - Width fraction	1-14/25 in
Physical Attribute - Socket Size	0.19
Dimension - Width mm	40 mm
Dimension - Width inch	1.56 in
Dimension - Length Overall inch	8.24 in

General

Insulation Type	Plastisol
Trade Name	UNITAP™
Material - Hardware	Aluminum
Insulation	Y
Physical Attribute - Screw Type	Allen
Plated	N
UPC	781810232736
Hex Key	3/16
Material	Aluminum

Plating Type	Unplated
UPC 12 Digit	781810232736
UPC 14 Digit GTIN	00781810232736

Operational	
Temperature Rating	194

Logistics

Minimum Pack Quantity	5
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)
[Catalog \[English\]](#)

