



BIBD2/04MT, Double Sided Mounted Four Conductor Clear Insulated Mult-Tap Connector

By Burndy

Catalog # [BIBD2/04MT](#)



Aluminum Multiple Tap Connector W/ Mount Holes, Clear Insulated, 4 Port, 2 Sided Entry, 14-2/0 Awg, Al/Cu Rated.

Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory

Application

Clear Insulated Multiple Tap Connectors Single- and Double-Sided Entry with Mounting Holes

General

Catalog Number	BIBD2/04MT
EU RoHS Indicator	Yes
Hex Key	3/16
Insulation	Y
Insulation Type	Plastisol
Material	Aluminum
Material - Hardware	Aluminum
Number Of Ports	4
Physical Attribute - Number of Screws	6
Physical Attribute - Screw Type	Allen
Sub Brand	UNITAP
Temperature Rating	194
Trade Name	UNITAP™
Type	BIBD-MT
UPC	781810253229
UPC 14 Digit GTIN	00781810253229

Dimensions

Dimension - Height fraction	1.5 in
Dimension - Height inch	1.50 in
Dimension - Height mm	38.1 mm
Dimension - Width fraction	1-14/25 in
Dimension - Width inch	1.56 in
Dimension - Width mm	40 mm

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - AL Str Size	8 AWG;6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG
Conductor - AL Str Size Range	8 AWG-2/0 AWG
Conductor - Copper Str Size Range	14 AWG - 2/0 AWG
Conductor Type	• AL C Str-Size • CU C Str-Size

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certification - UL Listed Direct Burial	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	100
Minimum Pack Quantity	1

Product Assets

- [3D Models - BIBD2-04MT_MODEL-PDF](#)
- [3D Models - BIBD2-04MT_MODEL-IGES](#)
- [3D Models - BIBD2-04MT_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Catalogs - UNITAP™ Products](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_BIBD-MT_LineArt](#)
- [Sales Drawings - SD213079-02_B](#)
- [Specifications - BIBD204MT](#)
- [Specifications - BURNDY_BIBD204MT_Specsheet](#)