



BIBD2/08FX, 2-Side, Flex, 8-Cond. Clear Ins. MultiTap

By Burndy
Catalog # [BIBD2/08FX](#)



Aluminum UNITAP, Double Sided Entry, #14-2/O Class B & C ,#14-
#1 Class G,H,I,K, DLO, 8 Port

Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory
- Suitable for Code and Flex Conductor
- Color-coordinated conductor port caps display wire range and classes of conductor accepted
- Screw port caps show installation torque information for easy reference

Specifications

Standards - Industry Standards	UL 486A-486B
Met	
Standards - RoHS Compliance	CM
Status	
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	14-2/O AWG
Conductor Type	• AL C Str-Size • CU C Str-Size

Configuration

Connector Type	Multi Tap
----------------	-----------

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

General

Plated	N
Trade Name	UNITAP™
UPC	621945439023
Insulation	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	621945439023
UPC 14 Digit GTIN	00621945439023

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	24

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)
[Catalog \[English\]](#)