



BIBD2504FX, 2-Side, Flex, 4-Cond. Clear Ins. MultiTap

By Burndy
Catalog # [BIBD2504FX](#)



Aluminum UNITAP, Mountable Double Sided Entry, #10-250 Class B & C ,#10-3/0 Class G,H,I,K, DLO, 4 Port

Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory
- Suitable for Code and Flex Conductor
- Color-coordinated conductor port caps display wire range and classes of conductor accepted
- Screw port caps show installation torque information for easy reference

Application

Tap connections and in-line splice/reductions are made quickly and easily with the UNITAP™ line of connectors

Specifications

Standards - Industry Standards	UL 486A-486B
Met	
Standards - RoHS Compliance	CM
Status	
Buy American Compliant	Under Review
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	10 AWG-250 KCMIL
Conductor Type	• AL C Str-Size • CU C Str-Size

Configuration

Connector Type	Multi Tap
Current	
Voltage - Maximum	600 V
Dimensions	
Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
General	
Plated	N
Trade Name	UNITAP™
Sub Brand	UNITAP
UPC	621945439009
Type	BIBD, Multi-Port
Insulation	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	621945439009
UPC 14 Digit GTIN	00621945439009

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1344
Carton Quantity	24

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)
[Catalog \[English\]](#)