



BIBD2504MT, 2-Side, Mount, 4-Cond. Clear Ins. MultiTap

By Burndy
Catalog # [BIBD2504MT](#)



#10 AWG - 250 kcmil, 4 Ports, Double-sided Entry, Al/Cu Rated, Mountable, Clear Plastisol allows visual confirmation conductor is properly inserted

Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - AL Str Size	• 8 AWG • 6 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil
Conductor - AL Str Size Range	8 AWG-250 kcmil
Conductor - Copper Str Size	• 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG

- 2 AWG
 - 1 AWG
 - 1/0
 - 2/0 AWG
 - 3/0 AWG
 - 4/0 AWG
 - 250 kcmil
- Conductor Size 10 AWG-250 KCMIL
- Conductor Type
- AL C Str-Size
 - CU C Str-Size
- Conductor - Copper Str Size Range 10 AWG - 250 kcmil

Configuration

Physical Attribute - Number of Screws	6
Number Of Ports	4
Connector Type	Multi Tap

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Height	0.000 in
Dimension - Height mm	57.4 mm
Dimension - Height inch	2.26 in
Dimension - Height fraction	2.25 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	147 mm
Dimension - Width fraction	2-16/25 in
Dimension - Width mm	67 mm
Dimension - Width inch	2.64 in
Dimension - Length Overall inch	5.78 in

General

Insulation Type	Plastisol
Trade Name	UNITAP™
Material - Hardware	Aluminum
Insulation	Y
Physical Attribute - Screw Type Plated	Allen N

UPC

Hex Key

Material

Plating Type

UPC 12 Digit

UPC 14 Digit GTIN

781810253281

5/16

Aluminum

Unplated

781810253281

00781810253281

Pallet Quantity

Carton Quantity

810

30

Operational

Temperature Rating

194

Product Assets

[Catalog \[English\]](#)

[Catalog \[English\]](#)

Logistics

Minimum Pack Quantity

1

