



# BIBD35010FX, 2-Side, Flex, 10-Cond. Clear Ins. MultiTap

By Burndy  
Catalog # [BIBD35010FX](#)



Aluminum UNITAP, Double Sided Entry, #10-350 Class B & C  
,#10-250 Class G,H,I,K, DLO, 10 Port

## Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory
- Suitable for Code and Flex Conductor
- Color-coordinated conductor port caps display wire range and classes of conductor accepted
- Screw port caps show installation torque information for easy reference

## Specifications

|                                |              |
|--------------------------------|--------------|
| Standards - Industry Standards | UL 486A-486B |
| Met                            |              |
| Standards - RoHS Compliance    | CM           |
| Status                         |              |
| Industry Standard(s)           | UL 486A-486B |
| UL Listed                      | Yes          |
| Certification - CSA Approved   | Yes          |

## Conductor

|                               |                                                                                         |
|-------------------------------|-----------------------------------------------------------------------------------------|
| Conductor Size                | 10 AWG-350 KCMIL                                                                        |
| Conductor - AL Str Size Range | 10AWG-250 kcmil                                                                         |
| Conductor Type                | <ul style="list-style-type: none"><li>• AL C Str-Size</li><li>• CU C Str-Size</li></ul> |

## Configuration

|                 |           |
|-----------------|-----------|
| Number Of Ports | 10        |
| Connector Type  | Multi Tap |

## Current

|                   |       |
|-------------------|-------|
| Amperage Rating   | 310 A |
| Voltage - Maximum | 600 V |

## Dimensions

|                            |           |
|----------------------------|-----------|
| Package Height             | 0.000 in  |
| Dimension - Height mm      | 0 mm      |
| Package Weight             | 0.000 lb. |
| Package Length             | 0.000 in  |
| Package Width              | 0.000 in  |
| Dimension - Length Overall | 9.250 in  |
| inch                       |           |

## General

|                   |                |
|-------------------|----------------|
| Plated            | Y              |
| Trade Name        | UNITAP™        |
| UPC               | 621945439146   |
| Insulation        | Y              |
| Material          | Aluminum       |
| Plating Type      | Tin            |
| UPC 12 Digit      | 621945439146   |
| UPC 14 Digit GTIN | 00621945439146 |

## Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

## Operational

|                    |                  |
|--------------------|------------------|
| Temperature Rating | -40° C to 135 °C |
|--------------------|------------------|

## Product Assets

[Catalog \[English\]](#)  
[Catalog \[English\]](#)



A Hubbell brand