



BIBD35010MT, 2-Side, Mount, 10-Cond. Clear Ins. MultiTap

By Burndy
Catalog # [BIBD35010MT](#)



#10 AWG - 350 kcmil, 10 Port, Double-sided Entry, Al/Cu Rated, Mountable, Clear Plastisol allows visual confirmation conductor is properly inserted

Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - AL Str Size	• 8 AWG • 6 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 266 kcmil • 300 kcmil • 336 kcmil • 350 kcmil
Conductor - AL Str Size Range	8 AWG-350 kcmil
Conductor - Copper Str Size	• 10 AWG • 9 AWG • 8 AWG • 7 AWG

- 6 AWG
 - 5 AWG
 - 4 AWG
 - 3 AWG
 - 2 AWG
 - 1 AWG
 - 1/0
 - 2/0 AWG
 - 3/0 AWG
 - 4/0 AWG
 - 250 kcmil
 - 300 kcmil
 - 350 kcmil
- Conductor Size 10 AWG-350 KCMIL
- Conductor Type
- AL C Str-Size
 - CU C Str-Size

Conductor - Copper Str Size Range 10 AWG - 350 kcmil

Configuration

Physical Attribute - Number of Screws	12
Number Of Ports	10
Connector Type	Multi Tap

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Height	0.000 in
Dimension - Height mm	66.8 mm
Dimension - Height inch	2.63 in
Dimension - Height fraction	2.625 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	288 mm
Dimension - Width mm	76 mm
Dimension - Width inch	3.00 in
Dimension - Length Overall inch	11.32 in

General

Insulation Type	Plastisol
-----------------	-----------

Trade Name	UNITAP™
Material - Hardware	Aluminum
Insulation	Y
Physical Attribute - Screw Type	Allen
Plated	N
UPC	781810253380
Hex Key	5/16
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810253380
UPC 14 Digit GTIN	00781810253380

Logistics

Minimum Pack Quantity	5
Pallet Quantity	405
Carton Quantity	15

Operational

Temperature Rating	194
--------------------	-----

Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)



A Hubbell brand