



BIBD3505, 2-Sided, 5-Cond. Clear Ins. MultiTap

By Burndy
Catalog # [BIBD3505](#)

#10 AWG - 350 kcmil, 5 Port, Double-sided Entry, Al/Cu Rated, Clear Plastisol allows visual confirmation conductor is properly inserted

Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory

Application

For Indoor Use Only, Copper Or Stranded Aluminum

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - AL Str Size	• 8 AWG • 6 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 266 kcmil • 300 kcmil • 336 kcmil • 350 kcmil
-------------------------	---



Conductor - AL Str Size Range	8 AWG-350 kcmil
Conductor - Copper Str Size	• 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil
Conductor Size	10 AWG-350 KCMIL
Conductor Type	• AL C Str-Size • CU C Str-Size
Conductor - Copper Str Size Range	10 AWG - 350 kcmil

Configuration

Physical Attribute - Number of Screws	5
Number Of Ports	5
Connector Type	Multi Tap

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Height	0.000 in
Dimension - Height mm	63.5 mm
Dimension - Height inch	2.50 in
Dimension - Height fraction	2.5 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	126 mm
Dimension - Width mm	76 mm
Dimension - Width inch	3.00 in

Dimension - Length Overall inch	4.95 in	Plating Type UPC 12 Digit UPC 14 Digit GTIN	Unplated 781810133460 00781810133460
General		Logistics	
Insulation Type	Plastisol	Pallet Quantity	1344
Trade Name	UNITAP™	Carton Quantity	24
Material - Hardware	Aluminum	Operational	
Insulation	Y	Temperature Rating	194
Physical Attribute - Screw Type	Allen	Product Assets	
Plated	N	Catalog [English]	
Sub Brand	UNITAP	Catalog [English]	
UPC	781810133460		
Type	BIBD, Multi-Port		
Hex Key	5/16		
Material	Aluminum		



A Hubbell brand