



BIBD3505FX, 2-Side, Flex, 5-Cond. Clear Ins. MultiTap



By Burndy
Catalog # [BIBD3505FX](#)

Aluminum UNITAP, Double Sided Entry, #10-350 Class B & C ,#10-250 Class G,H,I,K, DLO, 5 Port

Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory
- Suitable for Code and Flex Conductor
- Color-coordinated conductor port caps display wire range and classes of conductor accepted
- Screw port caps show installation torque information for easy reference

Specifications

Standards - Industry Standards	UL 486A-486B
Met	
Standards - RoHS Compliance	CM
Status	
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	10 AWG-350 KCMIL
Conductor - AL Str Size Range	10AWG-250 kcmil
Conductor Type	• AL C Str-Size • CU C Str-Size

Configuration

Number Of Ports	5
-----------------	---

Connector Type	Multi Tap
Current	
Amperage Rating	310 A
Voltage - Maximum	600 V
Dimensions	
Dimension - Height mm	0 mm
Dimension - Length Overall	4.7 in
General	
Plated	Y
Trade Name	UNITAP™
UPC	621945438675
Insulation	Y
Material	Aluminum
Plating Type	Tin
UPC 12 Digit	621945438675
UPC 14 Digit GTIN	00621945438675
Logistics	
Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1
Operational	
Temperature Rating	-40° C to 135 °C
Product Assets	
Catalog [English]	
Catalog [English]	