



BIBD3506MT, 2-Side, Mount, 6-Cond. Clear Ins. MultiTap

By Burndy
Catalog # [BIBD3506MT](#)



#10 AWG - 350 kcmil, 6 Port, Double-sided Entry, Al/Cu Rated, Mountable, Clear Plastisol allows visual confirmation conductor is properly inserted

Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory

Application

Clear Insulated Multiple Tap Connectors Single- and Double-Sided Entry with Mounting Holes

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - AL Str Size	• 8 AWG • 6 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 266 kcmil • 300 kcmil
-------------------------	---

Conductor - AL Str Size Range	• 336 kcmil • 350 kcmil
Conductor - Copper Str Size	8 AWG-350 kcmil
Conductor Size	• 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil
Conductor Type	10 AWG-350 KCMIL
Conductor - Copper Str Size Range	• AL C Str-Size • CU C Str-Size
Conductor - Copper Str Size Range	10 AWG - 350 kcmil

Configuration

Physical Attribute - Number of Screws	8
Number Of Ports	6
Connector Type	Multi Tap

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Height	0.000 in
Dimension - Height mm	66.8 mm
Dimension - Height inch	2.63 in
Dimension - Height fraction	2.625 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	195 mm

Dimension - Width mm	76 mm	Material	Aluminum
Dimension - Width inch	3.00 in	Plating Type	Unplated
Dimension - Length Overall inch	7.68 in	UPC 12 Digit	781810253342
		UPC 14 Digit GTIN	00781810253342
General		Logistics	
Insulation Type	Plastisol	Minimum Pack Quantity	1
Trade Name	UNITAP™	Pallet Quantity	1
Material - Hardware	Aluminum	Carton Quantity	1
Insulation	Y		
Physical Attribute - Screw Type	Allen	Operational	
Plated	N	Temperature Rating	194
Sub Brand	UNITAP		
UPC	781810253342	Product Assets	
Type	BIBD-MT	Catalog [English]	
Hex Key	5/16	Catalog [English]	



A Hubbell brand