



BIBD60010, 2-Side, 10-Cond. Clear Ins. MultiTap

By Burndy
Catalog # [BIBD60010](#)

#4 AWG - 600 kcmil, 10 Port, Double-sided Entry, Al/Cu Rated, Clear Plastisol allows visual confirmation conductor is properly inserted

Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory

Application

For Indoor Use Only, Copper Or Stranded Aluminum

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance	CM
Status	
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - AL Str Size	• 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 266 kcmil • 300 kcmil • 336 kcmil • 350 kcmil • 397 kcmil • 400 kcmil • 450 kcmil • 477 kcmil
-------------------------	---



Conductor - AL Str Size Range	• 500 kcmil • 550 kcmil • 556 kcmil • 600 kcmil
Conductor - Copper Str Size	4 AWG - 600 kcmil
Conductor Size	• 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil • 550 kcmil • 600 kcmil
Conductor Type	4 AWG-600 KCMIL
Conductor - Copper Str Size Range	• AL C Str-Size • CU C Str-Size

Configuration

Physical Attribute - Number of Screws	10
Number Of Ports	10
Connector Type	Multi Tap

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Height	0.000 in
Dimension - Height mm	69.9 mm
Dimension - Height inch	2.75 in
Dimension - Height fraction	2.75 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	329 mm
Dimension - Width mm	76 mm
Dimension - Width inch	3.00 in

Dimension - Length Overall inch	12.97 in	Plating Type	Unplated
General		UPC 12 Digit	781810232828
		UPC 14 Digit GTIN	00781810232828
Product Family	MECHANICAL	Logistics	
Insulation Type	Plastisol	Minimum Pack Quantity	1
Trade Name	UNITAP™	Pallet Quantity	320
Material - Hardware	Aluminum	Carton Quantity	10
Insulation	Y	Operational	
Physical Attribute - Screw Type	Allen	Temperature Rating	194
Plated	No	Product Assets	
Sub Brand	UNITAP	Catalog [English]	
Product Type	Run/Tap	Catalog [English]	
UPC	781810232828		
Type	BIBD, Multi-Port		
Hex Key	3/8		
Material	Aluminum		

