



BIBD60012MT, 2-Sided, Mount, 12-Cond. Clear Ins. MultiTap

By Burndy

Catalog # [BIBD60012MT](#)

#4 AWG - 600 kcmil, 12 Port, Double-sided Entry, Al/Cu Rated, Mountable, Clear Plastisol allows visual confirmation conductor is properly inserted



Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - AL Str Size	• 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 266 kcmil • 300 kcmil • 336 kcmil • 350 kcmil • 397 kcmil • 400 kcmil • 450 kcmil • 477 kcmil • 500 kcmil • 550 kcmil • 556 kcmil
-------------------------	---

Conductor - AL Str Size Range	• 600 kcmil
Conductor - Copper Str Size	4 AWG - 600 kcmil • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil • 550 kcmil • 600 kcmil
Conductor Size	4 AWG-600 KCMIL
Conductor Type	• AL C Str-Size • CU C Str-Size
Conductor - Copper Str Size Range	4 AWG - 600 kcmil

Configuration

Physical Attribute - Number of Screws	14
Number Of Ports	12
Connector Type	Multi Tap

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Height	0.000 in
Dimension - Height mm	73.2 mm
Dimension - Height inch	2.88 in
Dimension - Height fraction	2.875 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	459 mm
Dimension - Width mm	76 mm
Dimension - Width inch	3.00 in

Dimension - Length Overall inch	18.09 in	UPC 12 Digit UPC 14 Digit GTIN	781810253441 00781810253441
General		Logistics	
Insulation Type	Plastisol	Minimum Pack Quantity	5
Trade Name	UNITAP™	Pallet Quantity	224
Material - Hardware	Aluminum	Carton Quantity	8
Insulation	Y	Operational	
Physical Attribute - Screw Type	Allen	Temperature Rating	194
Plated	N	Product Assets	
UPC	781810253441	Catalog [English]	
Hex Key	3/8	Catalog [English]	
Material	Aluminum		
Plating Type	Unplated		



A Hubbell brand