



# BIBD60014, 2-Sided, 14-Cond. Clear Ins. MultiTap

By Burndy  
Catalog # BIBD60014



#4 AWG - 600 kcmil, 14 Port, Double-sided Entry, Al/Cu Rated, Clear Plastisol allows visual confirmation conductor is properly inserted

## Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory

## Application

Tap connections are made quickly and easily with the UNITAP line of connectors. UL486B Listed.Dual-rated AL9CU for any stranded copper or stranded aluminum applications

## Specifications

|                                         |              |
|-----------------------------------------|--------------|
| Certification - UL Recognized           | No           |
| Buy American Compliant                  | No           |
| Certification - cULus                   | No           |
| EU RoHS Indicator                       | Yes          |
| Industry Standard(s)                    | UL 486A-486B |
| Certification - ETL                     | No           |
| Standards - Industry Standards Met      | UL 486A-486B |
| Standards - RoHS Compliance Status      | CM           |
| Certification - UL Listed Direct Burial | No           |
| UL Listed                               | Yes          |
| Certification - CSA Approved            | Yes          |

## Conductor

|                         |                                                                                                                                                                                                                                                                 |
|-------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Conductor - AL Str Size | <ul style="list-style-type: none"><li>• 4 AWG</li><li>• 3 AWG</li><li>• 2 AWG</li><li>• 1 AWG</li><li>• 1/0 AWG</li><li>• 2/0 AWG</li><li>• 3/0 AWG</li><li>• 4/0 AWG</li><li>• 250 kcmil</li><li>• 266 kcmil</li><li>• 300 kcmil</li><li>• 336 kcmil</li></ul> |
|-------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

- 350 kcmil
- 397 kcmil
- 400 kcmil
- 450 kcmil
- 477 kcmil
- 500 kcmil
- 550 kcmil
- 556 kcmil
- 600 kcmil

Conductor - AL Str Size Range 4 AWG - 600 kcmil  
Conductor - Copper Str Size

- 4 AWG
- 3 AWG
- 2 AWG
- 1 AWG
- 1/0
- 2/0 AWG
- 3/0 AWG
- 4/0 AWG
- 250 kcmil
- 300 kcmil
- 350 kcmil
- 400 kcmil
- 450 kcmil
- 500 kcmil
- 550 kcmil
- 600 kcmil

Conductor Size 4 AWG-600 KCMIL  
Conductor Type

- AL C Str-Size
- CU C Str-Size

Conductor - Copper Str Size 4 AWG - 600 kcmil  
Range

## Configuration

|                                       |           |
|---------------------------------------|-----------|
| Physical Attribute - Number of Screws | 14        |
| Number Of Ports                       | 14        |
| Connector Type                        | Multi Tap |

## Current

|                   |       |
|-------------------|-------|
| Voltage Rating    | 600 V |
| Voltage - Maximum | 600 V |

## Dimensions

|                       |          |
|-----------------------|----------|
| Package Height        | 0.000 in |
| Dimension - Height mm | 69.9 mm  |

|                                 |                           |
|---------------------------------|---------------------------|
| Dimension - Height inch         | 2.75 in                   |
| Dimension - Height fraction     | 2.75 in                   |
| Package Weight                  | 0.000 lb.                 |
| Package Length                  | 0.000 in                  |
| Package Width                   | 0.000 in                  |
| Dimension - L Length Overall mm | 459 mm                    |
| Width                           | 3 in                      |
| Length                          | 18.09 in                  |
| Dimension - Width mm            | 76 mm                     |
| Dimension - Width inch          | 3.00 in                   |
| Height                          | 2.75 in                   |
| Dimension - Length Overall inch | 18.09 in                  |
| Dimensions                      | 18.09 in x 3 in x 2.75 in |

General

|                                 |           |
|---------------------------------|-----------|
| Insulation Type                 | Plastisol |
| Trade Name                      | UNITAP™   |
| Material - Hardware             | Aluminum  |
| Insulation                      | Y         |
| Physical Attribute - Screw Type | Allen     |

|                   |                |
|-------------------|----------------|
| Color             | Clear          |
| Plated            | N              |
| Sub Brand         | UNITAP         |
| UPC               | 781810232842   |
| Type              | BIBD           |
| Hex Key           | 3/8            |
| Material          | Aluminum       |
| Plating Type      | Unplated       |
| UPC 12 Digit      | 781810232842   |
| UPC 14 Digit GTIN | 00781810232842 |

Logistics

|                       |     |
|-----------------------|-----|
| Minimum Pack Quantity | 5   |
| Pallet Quantity       | 180 |
| Carton Quantity       | 12  |

Operational

|                    |     |
|--------------------|-----|
| Temperature Rating | 194 |
|--------------------|-----|

Product Assets

[Catalog \[English\]](#)  
[Catalog \[English\]](#)



A Hubbell brand