



BIBD6005FX, Double Sided Flex Rated Five Conductor Clear Insulated Mult-Tap Connector

By Burndy
Catalog # [BIBD6005FX](#)

Aluminum UNITAP, Mountable Double Sided Entry, #4-600 Class B & C ,#4-373 Class G,H,I,K, DLO, 5 PORT

Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory
- Suitable for Code and Flex Conductor
- Color-coordinated conductor port caps display wire range and classes of conductor accepted
- Screw port caps show installation torque information for easy reference

Specifications

Certification - CSA Approved	Yes
UL Listed	Yes
Standards - RoHS Compliance	CM
Status	



Conductor

Conductor Size	4 AWG-600 KCMIL
----------------	-----------------

Configuration

Connector Type	Multi Tap
----------------	-----------

Current

Voltage - Maximum	600 V
-------------------	-------

General

Material	Aluminum
UPC	621945439368

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)