



BIBD6006MT, 2-Side, Mount, 6-Cond. Clear Ins. MultiTap

By Burndy
Catalog # [BIBD6006MT](#)



#4 AWG - 600 kcmil, 6 Port, Double-sided Entry, Al/Cu Rated, Mountable, Clear Plastisol allows visual confirmation conductor is properly inserted

Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - AL Str Size	• 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 266 kcmil • 300 kcmil • 336 kcmil • 350 kcmil • 397 kcmil • 400 kcmil • 450 kcmil • 477 kcmil • 500 kcmil
-------------------------	---

Conductor - AL Str Size Range	• 550 kcmil • 556 kcmil • 600 kcmil
Conductor - Copper Str Size	4 AWG - 600 kcmil
Conductor Size	• 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil • 550 kcmil • 600 kcmil
Conductor Type	4 AWG-600 KCMIL
Conductor - Copper Str Size Range	• AL C Str-Size • CU C Str-Size
Conductor - Copper Str Size Range	4 AWG - 600 kcmil

Configuration

Physical Attribute - Number of Screws	8
Number Of Ports	6
Connector Type	Multi Tap

Current

Voltage - Maximum	600 V
Amperage Rating	780 A

Dimensions

Package Height	0.000 in
Dimension - Height mm	73.2 mm
Dimension - Height inch	2.88 in
Dimension - Height fraction	2.875 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

Dimension - L Length Overall mm 264 mm
Dimension - Width mm 76 mm
Dimension - Width inch 3.00 in
Dimension - Length Overall inch 10.41 in

General

Insulation Type Plastisol
Trade Name UNITAP™
Material - Hardware Aluminum
Insulation Y
Physical Attribute - Screw Type Allen
Plated N
Sub Brand UNITAP
UPC 781810253410
Type BIBD-MT

Hex Key 3/8
Material Aluminum
Plating Type Unplated
UPC 12 Digit 781810253410
UPC 14 Digit GTIN 00781810253410

Logistics

Minimum Pack Quantity 1
Pallet Quantity 480
Carton Quantity 15

Operational

Temperature Rating 194

Product Assets

[Catalog \[English\]](#)
[Catalog \[English\]](#)



A Hubbell brand