



BIBD75012, 2-Sided, 12-Cond. Clear Ins. MultiTap

By Burndy
Catalog # [BIBD75012](#)



#2 AWG -750 kcmil, 12 Port, Double-sided Entry, Al/Cu Rated, Clear Plastisol allows visual confirmation conductor is properly inserted

Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory

Application

Tap connections are made quickly and easily with the UNITAP line of connectors. UL486B Listed.Dual-rated AL9CU for any stranded copper or stranded aluminum applications.

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 266 kcmil • 300 kcmil • 336 kcmil • 350 kcmil • 397 kcmil
-------------------------	---

- 400 kcmil
- 450 kcmil
- 477 kcmil
- 500 kcmil
- 550 kcmil
- 556 kcmil
- 600 kcmil
- 636 kcmil
- 650 kcmil
- 700 kcmil
- 715 kcmil
- 750 kcmil

Conductor - AL Str Size Range	2 AWG - 750 kcmil
Conductor - Copper Str Size	• 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil • 550 kcmil • 600 kcmil • 700 kcmil • 750 kcmil

Conductor Size	2 AWG-750 KCMIL
Conductor Type	• AL C Str-Size • CU C Str-Size

Conductor - Copper Str Size Range	2 AWG - 750 kcmil
-----------------------------------	-------------------

Configuration

Physical Attribute - Number of Screws	12
Number Of Ports	12
Connector Type	Multi Tap

Current

Voltage Rating	600 V
Voltage - Maximum	600 V

Dimensions

Package Height	0.000 in
Dimension - Height mm	76.2 mm
Dimension - Height inch	3.00 in
Dimension - Height fraction	3 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	422 mm
Width	3.38 in
Dimension - Width fraction	3-19/50 in
Length	16.63 in
Dimension - Width mm	86 mm
Dimension - Width inch	3.38 in
Height	3 in
Dimension - Length Overall inch	16.63 in
Dimensions	16.63 in x 3.38 in x 3 in

General

Insulation Type	Plastisol
Trade Name	UNITAP™
Material - Hardware	Aluminum



A Hubbell brand

Insulation	Y
Physical Attribute - Screw Type	Allen
Color	Clear
Plated	N
Sub Brand	UNITAP
UPC	781810232910
Type	BIBD
Hex Key	3/8
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810232910
UPC 14 Digit GTIN	00781810232910

Logistics

Minimum Pack Quantity	1
Pallet Quantity	192
Carton Quantity	6

Operational

Temperature Rating	194
--------------------	-----

Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)