



BIBD75014, 2-Side, 14-Cond. Clear Ins. MultiTap

By Burndy
Catalog # [BIBD75014](#)

#2 AWG -750 kcmil, 14 Port, Double-sided Entry, Al/Cu Rated, Clear Plastisol allows visual confirmation conductor is properly inserted

Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 266 kcmil • 300 kcmil • 336 kcmil • 350 kcmil • 397 kcmil • 400 kcmil • 450 kcmil • 477 kcmil • 500 kcmil • 550 kcmil • 556 kcmil • 600 kcmil • 636 kcmil
-------------------------	---



Conductor - AL Str Size Range	• 650 kcmil • 700 kcmil • 715 kcmil • 750 kcmil
Conductor - Copper Str Size	2 AWG - 750 kcmil
Conductor Size	• 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil • 550 kcmil • 600 kcmil • 700 kcmil • 750 kcmil
Conductor Type	2 AWG-750 KCMIL
Conductor - Copper Str Size Range	• AL C Str-Size • CU C Str-Size

Configuration

Physical Attribute - Number of Screws	14
Number Of Ports	14
Connector Type	Multi Tap

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Height	0.000 in
Dimension - Height mm	76.2 mm
Dimension - Height inch	3.00 in
Dimension - Height fraction	3 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

Dimension - L Length Overall mm	492 mm	Material	Aluminum
Dimension - Width fraction	3-19/50 in	Plating Type	Unplated
Dimension - Width mm	86 mm	UPC 12 Digit	781810232927
Dimension - Width inch	3.38 in	UPC 14 Digit GTIN	00781810232927
Dimension - Length Overall inch	19.37 in		
General		Logistics	
Insulation Type	Plastisol	Minimum Pack Quantity	1
Trade Name	UNITAP™	Pallet Quantity	75
Material - Hardware	Aluminum	Carton Quantity	5
Insulation	Y		
Physical Attribute - Screw Type	Allen	Operational	
Plated	N	Temperature Rating	194
UPC	781810232927	Product Assets	
Hex Key	3/8	Catalog [English]	
		Catalog [English]	



A Hubbell brand