



BIBD7506, 2-Side, 6-Cond. Clear Ins., MultiTap

By Burndy
Catalog # [BIBD7506](#)



#2 AWG -750 kcmil, 6 Port, Double-sided Entry, Al/Cu Rated, Clear Plastisol allows visual confirmation conductor is properly inserted

Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory

Application

For Indoor Use Only, Copper Or Stranded Aluminum

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance	CM
Status	
Certification - UL Listed Direct Burial	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 266 kcmil • 300 kcmil • 336 kcmil • 350 kcmil • 397 kcmil • 400 kcmil • 450 kcmil • 477 kcmil • 500 kcmil • 550 kcmil
-------------------------	---

Conductor - AL Str Size Range	• 556 kcmil • 600 kcmil • 636 kcmil • 650 kcmil • 700 kcmil • 715 kcmil • 750 kcmil
Conductor - Copper Str Size	2 AWG - 750 kcmil • 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil • 550 kcmil • 600 kcmil • 700 kcmil • 750 kcmil
Conductor Size	2 AWG-750 KCMIL
Conductor Type	• AL C Str-Size • CU C Str-Size
Conductor - Copper Str Size Range	2 AWG - 750 kcmil

Configuration

Physical Attribute - Number of Screws	6
Number Of Ports	6
Connector Type	Multi Tap

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Height	0.000 in
Dimension - Height mm	76.2 mm
Dimension - Height inch	3.00 in
Dimension - Height fraction	3 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

Dimension - L Length Overall mm	213 mm	Hex Key	3/8
Dimension - Width fraction	3-19/50 in	Material	Aluminum
Dimension - Width mm	86 mm	Plating Type	Unplated
Dimension - Width inch	3.38 in	UPC 12 Digit	781810232880
Dimension - Length Overall inch	8.37 in	UPC 14 Digit GTIN	00781810232880
General		Logistics	
Product Family	MECHANICAL	Minimum Pack Quantity	1
Insulation Type	Plastisol	Pallet Quantity	432
Trade Name	UNITAP™	Carton Quantity	12
Material - Hardware	Aluminum	Operational	
Insulation	Y	Temperature Rating	194
Physical Attribute - Screw Type	Allen	Product Assets	
Plated	No	Catalog [English]	
Sub Brand	UNITAP	Catalog [English]	
Product Type	Run/Tap		
UPC	781810232880		
Type	BiBD, Multi-Port		

