



BIBD7508FX, 2-Side, Flex, 8-Cond. Clear Ins. MultiTap

By Burndy
Catalog # [BIBD7508FX](#)



Aluminum UNITAP, Double Sided Entry, #2 - 750 Class B & C ,#2
- 535 Class G,H,I,K,DLO, 8 Ports

Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory
- Suitable for Code and Flex Conductor
- Color-coordinated conductor port caps display wire range and classes of conductor accepted
- Screw port caps show installation torque information for easy reference

Specifications

Standards - Industry Standards	UL 486A-486B
Met	
Standards - RoHS Compliance	CM
Status	
Industry Standard(s)	UL 486A-486B

Conductor

Conductor Size	2 AWG-750 KCMIL
Conductor - AL Str Size Range	2 AWG-535 kcmil
Conductor Type	• AL C Str-Size • CU C Str-Size

Configuration

Number Of Ports	8
Connector Type	Multi Tap

Current

Amperage Rating	475 A
Voltage - Maximum	600 V

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Length Overall	10.875 in
inch	

General

Plated	Y
Color Code	Black
Trade Name	UNITAP™
UPC	621945439276
Insulation	Y
Material	Aluminum
Plating Type	Tin
UPC 12 Digit	621945439276
UPC 14 Digit GTIN	00621945439276

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Operational

Temperature Rating	-40° C to 135 °C
--------------------	------------------

Product Assets

[Catalog \[English\]](#)
[Catalog \[English\]](#)