



BIBS2/012, 12-Cond. Clear Ins. Multi-Tap

By Burndy
Catalog # BIBS2/012

#14 - 2/0 AWG, 12 Ports, Single-sided Entry, Al/Cu Rated, Clear
Plastisol allows visual confirmation conductor is properly inserted



Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory

- 6 AWG
- 5 AWG
- 4 AWG
- 3 AWG
- 2 AWG
- 1 AWG
- 1/0
- 2/0 Str

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	No
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	14-2/0 AWG
Conductor - AL Str Size	• 8 AWG • 6 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG
Conductor - AL Str Size Range	8 AWG-2/0 AWG
Conductor Type	• AL C Str-Size • CU C Str-Size
Conductor - Copper Str Size Range	14 AWG - 2/0 AWG
Conductor - Copper Str Size	• 14 AWG • 12 AWG • 10 AWG • 9 AWG • 8 AWG • 7 AWG

Configuration

Physical Attribute - Number of Screws	12
Number Of Ports	12
Connector Type	Multi Tap

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Height	0.000 in
Dimension - Height mm	35.1 mm
Dimension - Height inch	1.38 in
Dimension - Height fraction	1.375 in
Package Weight	0.000 lb.
Dimension - Width mm	33 mm
Dimension - Width inch	1.31 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	209 mm
Dimension - Width fraction	1-31/100 in
Dimension - Length Overall inch	8.24 in

General

Physical Attribute - Screw Type	Allen
Plated	N
Insulation Type	Plastisol
Trade Name	UNITAP™
Material - Hardware	Aluminum
UPC	781810232941
Insulation	Y
Hex Key	3/16
Material	Aluminum
Plating Type	Unplated

UPC 12 Digit781810232941

UPC 14 Digit GTIN00781810232941

Operational

Temperature Rating194

Logistics

Minimum Pack Quantity5

Pallet Quantity4050

Carton Quantity150

Product Assets

Catalog [English]

Catalog [English]

