



BIBS2/012MT, Mount, 12-Cond. Clear Ins.  
MultiTap

By Burndy  
Catalog # [BIBS2/012MT](#)



#14 - 2/0 AWG, 12 Ports, Single-sided Entry, Al/Cu Rated,  
Mountable, Clear Plastisol allows visual confirmation conductor is  
properly inserted

Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory

Specifications

|                                         |       |
|-----------------------------------------|-------|
| Certification - ETL                     | No    |
| Certification - UL Recognized           | No    |
| Standards - Industry Standards Met      | UL467 |
| Standards - RoHS Compliance Status      | CM    |
| Certification - cULus                   | No    |
| Certification - UL Listed Direct Burial | No    |
| Industry Standard(s)                    | UL467 |
| UL Listed                               | Yes   |
| Certification - CSA Approved            | Yes   |

Conductor

|                                   |                                                                                                                                                                             |
|-----------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Conductor Size                    | 14-2/0 AWG                                                                                                                                                                  |
| Conductor - AL Str Size           | <ul style="list-style-type: none"><li>• 8 AWG</li><li>• 6 AWG</li><li>• 4 AWG</li><li>• 3 AWG</li><li>• 2 AWG</li><li>• 1 AWG</li><li>• 1/0 AWG</li><li>• 2/0 AWG</li></ul> |
| Conductor - AL Str Size Range     | 8 AWG-2/0 AWG                                                                                                                                                               |
| Conductor Type                    | <ul style="list-style-type: none"><li>• AL C Str-Size</li><li>• CU C Str-Size</li></ul>                                                                                     |
| Conductor - Copper Str Size Range | 14 AWG - 2/0 AWG                                                                                                                                                            |
| Conductor - Copper Str Size       | <ul style="list-style-type: none"><li>• 14 AWG</li><li>• 12 AWG</li><li>• 10 AWG</li><li>• 9 AWG</li><li>• 8 AWG</li><li>• 7 AWG</li></ul>                                  |

- 6 AWG
- 5 AWG
- 4 AWG
- 3 AWG
- 2 AWG
- 1 AWG
- 1/0
- 2/0 Str

Configuration

|                                       |           |
|---------------------------------------|-----------|
| Physical Attribute - Number of Screws | 14        |
| Number Of Ports                       | 12        |
| Connector Type                        | Multi Tap |

Current

|                   |       |
|-------------------|-------|
| Voltage - Maximum | 600 V |
|-------------------|-------|

Dimensions

|                                 |                            |
|---------------------------------|----------------------------|
| Package Height                  | 0.000 in                   |
| Dimension - Height mm           | 38.1 mm                    |
| Length                          | 9.58 in                    |
| Dimension - Height inch         | 1.50 in                    |
| Dimension - Height fraction     | 1.5 in                     |
| Package Weight                  | 0.000 lb.                  |
| Dimension - Width mm            | 32 mm                      |
| Dimension - Width inch          | 1.25 in                    |
| Package Length                  | 0.000 in                   |
| Package Width                   | 0.000 in                   |
| Dimension - L Length Overall mm | 243 mm                     |
| Height                          | 1.5 in                     |
| Width                           | 1.25 in                    |
| Dimension - Width fraction      | 1-31/100 in                |
| Dimension - Length Overall inch | 9.58 in                    |
| Dimensions                      | 9.58 in x 1.25 in x 1.5 in |

General

|                                 |              |
|---------------------------------|--------------|
| Physical Attribute - Screw Type | Allen        |
| Plated                          | N            |
| Insulation Type                 | Plastisol    |
| Trade Name                      | UNITAP™      |
| Material - Hardware             | Aluminum     |
| UPC                             | 781810252901 |

|                   |                |
|-------------------|----------------|
| Insulation        | Y              |
| Hex Key           | 3/16           |
| Material          | Aluminum       |
| Plating Type      | Unplated       |
| UPC 12 Digit      | 781810252901   |
| UPC 14 Digit GTIN | 00781810252901 |

Logistics



A Hubbell brand

Minimum Pack Quantity 5

Operational

Temperature Rating 194

Product Assets

[Catalog \[English\]](#)

[Catalog \[English\]](#)