

BIBS2/014FX, Flex, 14-Cond. Clear Ins. MultiTap

By Burndy

Catalog # [BIBS2/014FX](#)

Aluminum UNITAP, Single-Sided, #14 - 2/O Class B & C, #14 - #1 Class G,H,I,K, DLO, 14 Port



Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory
- Suitable for Code and Flex Conductor
- Color-coordinated conductor port caps display wire range and classes of conductor accepted
- Screw port caps show installation torque information for easy reference

Specifications

Standards - Industry Standards	UL 486A-486B
Met	
Standards - RoHS Compliance	CM
Status	
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	14-2/O AWG
Conductor - AL Str Size Range	1 AWG - 14 AWG
Conductor Type	• AL C Str-Size • CU C Str-Size

Configuration

Number Of Ports	14
Connector Type	Multi Tap

Current

Amperage Rating	175 A
Voltage - Maximum	600 V

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Length Overall	9.330 in
inch	

General

Plated	Y
Color Code	Black
Trade Name	UNITAP™
UPC	621945439306
Insulation	Y
Material	Aluminum
Plating Type	Tin
UPC 12 Digit	621945439306
UPC 14 Digit GTIN	00621945439306

Logistics

Minimum Pack Quantity	5
Pallet Quantity	1
Carton Quantity	1

Operational

Temperature Rating	-40° C to 135 °C
--------------------	------------------

Product Assets

[Catalog \[English\]](#)

[Catalog \[English\]](#)