



BIBS2/04MT, Mount, 4-Cond. Clear Ins. MultiTap

By Burndy
Catalog # [BIBS2/04MT](#)



#14 - 2/0 AWG, 4 Ports, Single-sided Entry, Al/Cu Rated, Mountable, Clear Plastisol allows visual confirmation conductor is properly inserted

Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - AL Str Size	• 8 AWG • 6 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG
Conductor - AL Str Size Range	8 AWG - 2/0 AWG
Conductor - Copper Str Size	• #14 • 12 AWG • 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG

Conductor Size	• 1 AWG • 1/0 • 2/0 Str
Conductor Type	14-2/0 AWG • AL C Str-Size • CU C Str-Size
Conductor - Copper Str Size Range	14 AWG - 2/0 AWG

Configuration

Physical Attribute - Number of Screws	6
Number Of Ports	4
Connector Type	Multi Tap

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Height	0.000 in
Dimension - Height mm	38.1 mm
Dimension - Height inch	1.50 in
Dimension - Height fraction	1.5 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	107 mm
Width	1.25 in
Dimension - Width fraction	1-31/100 in
Length	4.2 in
Dimension - Width mm	32 mm
Dimension - Width inch	1.25 in
Height	1.5 in
Dimension - Length Overall inch	4.20 in
Dimensions	4.2 in x 1.25 in x 1.5 in

General

Insulation Type	Plastisol
Trade Name	UNITAP™
Material - Hardware	Aluminum
Insulation	Y
Physical Attribute - Screw Type Plated	Allen N

UPC	781810252765
Hex Key	3/16
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810252765
UPC 14 Digit GTIN	00781810252765

Pallet Quantity	5200
Carton Quantity	100

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)
[Catalog \[English\]](#)

Logistics

Minimum Pack Quantity	1
-----------------------	---



A Hubbell brand