



BIBS2/06FX, Single Sided Flex Rated Six Conductor Clear Insulated Mult-Tap Connector

By Burndy
Catalog # [BIBS2/06FX](#)



Aluminum UNITAP, Single Sided Entry, #14-2/0 Class B & C
,#14-#1 Class G,H,I,K, DLO, 6 PORT.

Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory
- Suitable for Code and Flex Conductor
- Color-coordinated conductor port caps display wire range and classes of conductor accepted
- Screw port caps show installation torque information for easy reference

General

Color Code	Black
Connector Type	Multi Tap
Insulation	Y
Material	Aluminum
Number Of Ports	6
Plated	Y
Plating Type	Tin
Temperature Rating	-40° C to 135 °C
Trade Name	UNITAP™
UPC	621945439542
UPC 12 Digit	6219454395422

Dimensions

Dimension - Length Overall	3.954 in
inch	

Electrical Ratings

Amperage Rating	175 A
Voltage - Maximum	600 V

Conductor Related

Conductor - AL Str Size Range	1 AWG - 14 AWG
Conductor Size	14-2/0 AWG
Conductor Type	• AL C Str-Size • CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - UNITAP™ Products](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50046931](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-BIBS2/06FX-SPEC-EN | REV 5/2024