



BIBS25012MT, Mount, 12-Cond. Clear Ins. MultiTap

By Burndy
Catalog # [BIBS25012MT](#)

#10 AWG - 250 kcmil, 12 Ports, Single-sided Entry, Al/Cu Rated, Mountable, Clear Plastisol allows visual confirmation conductor is properly inserted

Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	No
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	10 AWG-250 KCMIL
Conductor - AL Str Size Range	10 AWG - 250 kcmil
Conductor Type	• AL C Str-Size • CU C Str-Size
Conductor - Copper Str Size Range	10 AWG - 250 kcmil

Configuration

Physical Attribute - Number of Screws	14
Number Of Ports	12
Connector Type	Multi Tap

Current

Operating Voltage	600 V
Voltage - Maximum	600 V

Dimensions

Dimension - Height mm	67 mm
Length	13.28 in
Dimension - Height inch	2.63 in
Dimension - Width mm	50 mm
Dimension - Width inch	1.95 in
Dimension - L Length Overall mm	337 mm
Height	2.63 in
Width	1.95 in
Dimension - Length Overall inch	13.28 in
Dimensions	13.28 in x 1.95 in x 2.63 in

General

Physical Attribute - Screw Type	Allen
Plated	N
Insulation Type	Plastisol
Trade Name	UNITAP™
UPC	781810252994
Insulation	Y
Hex Key	5/16
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810252994
UPC 14 Digit GTIN	00781810252994

Logistics

Minimum Pack Quantity	5
-----------------------	---

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)
[Catalog \[English\]](#)