



BIBS3504DB, Direct Burial Submersible, 4-Cond. Ins.

By Burndy

Catalog # [BIBS3504DB](#)

Direct Burial UNITAP, 4-Conductor, Single-Sided, #12 AWG-350 kcmil, Dual Rated, EPDM Rubber Covering,



Features

- Dual rated for aluminum or copper conductors
- Each unit individually marked for ease of identification
- Supplied with aluminum set-screws
- Supplied with oxide inhibitor pre-installed
- Submersible rated and suitable for Direct Burial

Application

For Outside Direct Burial

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	12 AWG-350 KCMIL
Conductor - AL Str Size Range	12 - 350 Str
Conductor Type	• AL C Str-Size • CU C Str-Size
Conductor - Copper Str Size Range	12 - 350 Str

Configuration

Number Of Ports	4
Connector Type	Multi Tap

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Height	0.000 in
----------------	----------

Dimension - Height mm	62 mm
Dimension - Height inch	2.46 in
Package Weight	0.000 lb.
Dimension - Width mm	103 mm
Dimension - Width inch	4.06 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	128 mm
Dimension - Length Overall inch	5.03 in
Dimension - Strip Length inch	1.125

Force Related

Installation Torque	450 LBS/in
Recommended in-lb	

General

Plated	N
Trade Name	UNITAP™
Sub Brand	UNITAP
UPC	781810523605
Type	BIBS, Multi-Port - Direct Burial
Insulation	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810523605
UPC 14 Digit GTIN	00781810523605

Logistics

Pallet Quantity	672
Carton Quantity	12

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)
[Catalog \[English\]](#)



A Hubbell brand