

BIBS3505DB, Direct Burial Submersible, 5-Cond. Ins.

By Burndy
Catalog # [BIBS3505DB](#)

Direct Burial UNITAP, 5-Conductor, Single-Sided, #12 AWG-350 kcmil,
Dual Rated, EPDM Rubber Covering,



Features

- Dual rated for aluminum or copper conductors
- Each unit individually marked for ease of identification
- Supplied with aluminum set-screws
- Supplied with oxide inhibitor pre-installed
- Submersible rated and suitable for Direct Burial

Application

For Outside Direct Burial

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
Buy America(n) Qualified	BABA Compliant (All status valid till December 2026)
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - AL Str Size Range	12 AWG - 350 kcmil
Conductor Size	12 AWG-350 KCMIL
Conductor Type	• AL C Str-Size • CU C Str-Size
Conductor - Copper Str Size Range	12 AWG - 350 kcmil

Configuration

Number Of Ports	5
Connector Type	Multi Tap

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Height	0.000 in
----------------	----------

Dimension - Height mm	62 mm
Dimension - Height inch	2.46 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	158 mm
Dimension - Strip Length inch	1.125
Dimension - Width mm	103 mm
Dimension - Width inch	4.06 in
Dimension - Length Overall inch	6.24 in

Force Related

Installation Torque Recommended	450 LBS/in in-lb
---------------------------------	------------------

General

Product Family	MECHANICAL
Trade Name	UNITAP™
Insulation	Y
Plated	No
Sub Brand	UNITAP
Product Type	Run/Tap
UPC	781810523612
Type	BIBS, Multi-Port - Direct Burial
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810523612
UPC 14 Digit GTIN	00781810523612

Logistics

Minimum Pack Quantity	1
Pallet Quantity	672
Carton Quantity	12

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)
[Catalog \[English\]](#)