

BIBS3506, 6-Cond. Clear Ins. Multi-Tap, Al/Cu Rated

By Burndy
Catalog # [BIBS3506](#)

#10 AWG - 350 kcmil, 6 Ports, Single-sided Entry, Al/Cu Rated, Clear
Plastisol allows visual confirmation conductor is properly inserted

Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory

Application

For Indoor Use Only, Copper Or Stranded Aluminum

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance	CM
Status	
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - AL Str Size Range	10 AWG - 350 kcmil
Conductor Size	10 AWG-350 KCMIL
Conductor Type	• AL C Str-Size • CU C Str-Size
Conductor - Copper Str Size Range	10 AWG - 350 kcmil

Configuration

Physical Attribute - Number of Screws	10
Number Of Ports	6
Connector Type	Multi Tap

Current



Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Height	0.000 in
Dimension - Height mm	64 mm
Dimension - Height inch	2.50 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	149 mm
Dimension - Width mm	59 mm
Dimension - Width inch	2.32 in
Dimension - Length Overall inch	5.86 in

General

Product Family	MECHANICAL
Insulation Type	Plastisol
Trade Name	UNITAP™
Insulation	Y
Physical Attribute - Screw Type	Allen
Plated	No
Sub Brand	UNITAP
Product Type	Run/Tap
UPC	781810133514
Type	BIBS, Multi-Port
Hex Key	5/16
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810133514
UPC 14 Digit GTIN	00781810133514

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1344
Carton Quantity	42

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)
[Catalog \[English\]](#)