

BIBS46, 6-Cond., 1-Side, Clear Ins. Multi-Tap

By Burndy
Catalog # [BIBS46](#)

Aluminum Multiple Tap Connector, Clear Insulated, 6 Port, 1 Sided Entry, 14-4 AWG, Al/Cu Rated



Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory

Application

For Indoor Use Only, Copper Or Stranded Aluminum

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - AL Str Size Range	14 AWG - 4 AWG
Conductor Size	14-4 AWG
Conductor Type	• AL C Str-Size • CU C Str-Size
Conductor - Copper Str Size Range	14 AWG - 4 AWG

Configuration

Physical Attribute - Number of Screws	6
Number Of Ports	6
Connector Type	Multi Tap

Current

Operating Voltage	600 V
Voltage - Maximum	600 V

Dimensions

Package Height	0.000 in
Dimension - Height mm	31.8 mm
Dimension - Height inch	1.25 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	72 mm
Dimension - Screw Size inch	1/4
Dimension - Width mm	32 mm
Dimension - Width inch	1.25 in
Dimension - Length Overall inch	2.83 in

General

Insulation Type	Plastisol
Trade Name	UNITAP™
Insulation	Y
Physical Attribute - Screw Type	Allen
Plated	N
Sub Brand	UNITAP
UPC	781810223840
Type	BIBS, Multi-Port
Hex Key	1/8
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810223840
UPC 14 Digit GTIN	00781810223840

Logistics

Pallet Quantity	6336
Carton Quantity	99

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)
[Catalog \[English\]](#)