



BIBS6003FX, Flex, 3-Cond. Clear Ins. MultiTap

By Burndy

Catalog # [BIBS6003FX](#)

Aluminum UNITAP, Single Sided Entry, #4-600 Class B & C ,#4-373 Class G,H,I,K, DLO, 3 Port



Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory
- Suitable for Code and Flex Conductor
- Color-coordinated conductor port caps display wire range and classes of conductor accepted
- Screw port caps show installation torque information for easy reference


Specifications

Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper DLO Size Range	4 - 373 Str
Conductor Size	4 AWG-600 KCMIL
Conductor - Copper Flex G Size Range	4 - 373 Str
Conductor - Copper Flex K Size Range	4 - 373 Str
Conductor Type	• AL C Str-Size • CU C Str-Size • CU C Fex-Size
Conductor - Copper Str Size Range	4 AWG - 600 kcmil
Conductor - Copper Flex H Size Range	4 - 373 Str
Conductor - Copper Flex I Size Range	4 - 373 Str

Configuration



Number Of Ports	3
Connector Type	Multi Tap

Current

Operating Voltage	600 V
Voltage - Maximum	600 V

Dimensions

Package Height	0.000 in
Dimension - Height mm	70 mm
Dimension - Height inch	2.75 in
Package Weight	0.000 lb.
Dimension - Width mm	60 mm
Dimension - Width inch	2.38 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	95.25 mm
Dimension - Length Overall inch	3.75 in

General

Plated	Y
Color Code	Green
Trade Name	UNITAP™
UPC	621945439849
Insulation	Y
Material	Aluminum
Plating Type	Tin Plated Aluminum
UPC 12 Digit	621945439849
UPC 14 Digit GTIN	00621945439849

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1280
Carton Quantity	40

Operational

Temperature Rating	135°C
--------------------	-------

Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)