


BIBS6008MT, Mount, 8-Cond. Clear Ins. MultiTap

By Burndy
Catalog # [BIBS6008MT](#)

Aluminum UNITAP, Mountable, Single Sided Entry, 8 Port, #4
AWG-600 kcmil, Al/Cu Rated



Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	No
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	4 AWG-600 KCMIL
Conductor - AL Str Size Range	4 AWG - 600 kcmil
Conductor Type	• AL C Str-Size • CU C Str-Size
Conductor - Copper Str Size Range	4 AWG - 600 kcmil

Configuration

Physical Attribute - Number of Screws	10
Number Of Ports	8
Connector Type	Multi Tap

Current

Operating Voltage	600 V
Voltage - Maximum	600 V

Dimensions

Package Height	0.000 in
Dimension - Height mm	73 mm
Length	12.97 in
Dimension - Height inch	2.88 in
Package Weight	0.000 lb.
Dimension - Width mm	57 mm
Dimension - Width inch	2.25 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	329 mm
Height	2.88 in
Width	2.25 in
Dimension - Length Overall inch	12.97 in
Dimensions	12.97 in x 2.25 in x 2.88 in

General

Physical Attribute - Screw Type	Allen
Plated	N
Insulation Type	Plastisol
Trade Name	UNITAP™
UPC	781810253199
Insulation	Y
Hex Key	3/8
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810253199
UPC 14 Digit GTIN	00781810253199

Logistics

Minimum Pack Quantity	5
Pallet Quantity	324
Carton Quantity	12

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)
[Catalog \[English\]](#)

