



BIBS7503FX, Flex, 3-Cond. Clear Ins.
MultiTap

By Burndy
Catalog # [BIBS7503FX](#)



Aluminum Multiple Tap Connector, Single Sided Entry, #2 AWG-750 kcmil, 3 Port

Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory
- Suitable for Code and Flex Conductor
- Color-coordinated conductor port caps display wire range and classes of conductor accepted
- Screw port caps show installation torque information for easy reference

Specifications

Standards - Industry Standards	UL 486A-486B
Met	
Standards - RoHS Compliance	CM
Status	
Industry Standard(s)	UL 486A-486B

Conductor

Conductor - Copper DLO Size Range	2 - 535 Str
Conductor Size	2 AWG-750 KCMIL
Conductor - Copper Flex G Size Range	2 - 535 Str
Conductor - Copper Flex K Size Range	2 - 535 Str
Conductor Type	• AL C Str-Size • CU C Str-Size • CU C Fex-Size
Conductor - Copper Str Size Range	2 - 750 Str
Conductor - Copper Flex H Size Range	2 - 535 Str
Conductor - Copper Flex I Size Range	2 - 535 Str

Configuration

Number Of Ports	3
-----------------	---

Connector Type	Multi Tap
----------------	-----------

Current

Operating Voltage	600 V
Voltage - Maximum	600 V

Dimensions

Package Height	0.000 in
Dimension - Height mm	76 mm
Dimension - Height inch	3 in
Package Weight	0.000 lb.
Dimension - Width mm	70 mm
Dimension - Width inch	2.75 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	101.6 mm
Dimension - Length Overall inch	4 in

General

Plated	Y
Color Code	Black
Trade Name	UNITAP™
UPC	621945439924
Insulation	Y
Material	Aluminum
Plating Type	Tin Plated Aluminum
UPC 12 Digit	621945439924
UPC 14 Digit GTIN	00621945439924

Logistics

Pallet Quantity	1
Carton Quantity	1

Operational

Temperature Rating	135°C
--------------------	-------

Product Assets

[Catalog \[English\]](#)
[Catalog \[English\]](#)