



BISR350, Clear Insulated Splice Reducer, #10 AWG - 350 kcmil

By Burndy
Catalog # [BISR350](#)

Aluminum UNITAP In-Line Splice Reducer, Clear Insulation, #10
AWG - 350 kcmil



Features

- Type BISR In-Line Splice/Reducers are easily installed on code conductor
- UL486B Listed, Dual rated AL9CU for any stranded copper or stranded aluminum applications

Application

For Indoor Use Only

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - AL Str Size	• 8 AWG • 6 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 266 kcmil • 300 kcmil • 336 kcmil • 350 kcmil
Conductor - AL Str Size Range	10 AWG - 350 kcmil
Conductor - Copper Str Size	• #10 • 9 AWG • 8 AWG • 7 AWG

- 6 AWG
 - 5 AWG
 - 4 AWG
 - 3 AWG
 - 2 AWG
 - 1 AWG
 - 1/0
 - 2/0 AWG
 - 3/0 AWG
 - 4/0 AWG
 - 250 kcmil
 - 300 kcmil
 - 350
- Conductor Size 10 AWG-350 KCMIL
- Conductor Type
- AL C Str-Size
 - CU C Str-Size

Conductor - Copper Str Size Range 10 AWG - 350 kcmil

Configuration

Physical Attribute - Number of Screws	2
Number Of Ports	2
Connector Type	In-Line

Current

Operating Voltage	600 V
Voltage - Maximum	600 V

Dimensions

Package Height	0.000 in
Dimension - Height mm	60 mm
Dimension - Height inch	2.35 in
Dimension - Height fraction	2.3333333333333335 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	118 mm
Dimension - Width fraction	1-17/50 in
Dimension - Width mm	34 mm
Dimension - Width inch	1.34 in
Dimension - Length Overall inch	4.63 in

General

Insulation Type	Plastisol	UPC 14 Digit GTIN	00781810134092
Trade Name	UNITAP™	Logistics	
Material - Hardware	Aluminum		
Insulation	Y		
Physical Attribute - Screw Type	Allen	Pallet Quantity	2160
Plated	N	Carton Quantity	60
Sub Brand	UNITAP	Operational	
UPC	781810134092		
Type	BISR, In-Line	Temperature Rating	90 °C
Hex Key	5/16 in	Product Assets	
Material	Aluminum		
Plating Type	Unplated		
UPC 12 Digit	781810134092	Catalog [English]	
		Catalog [English]	



A Hubbell brand