



BIT350, 1-Side, 2-Cond. Clear Ins., MultiTap

By Burndy
Catalog # [BIT350](#)

Aluminum Multiple Tap Connector, Clear Insulated, 2 Port, 1 Sided Entry, 10 AWG-350 kcmil, Al/Cu Rated



Features

- Type BIT and BITO (Offset) Multi-tap connectors are installed quickly and easily
- Suitable for use on Code conductor
- UL486B Listed, Dual-rated AL9CU.

Application

For Indoor Use Only, Copper Or Stranded Aluminum

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - AL Str Size	• 8 AWG • 6 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil
Conductor - AL Str Size Range	10 AWG - 350 kcmil
Conductor - Copper Str Size	• 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG

Conductor Size	• 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil
Conductor Type	• 10 AWG-350 KCMIL • AL C Str-Size • CU C Str-Size
Conductor - Copper Str Size Range	10 AWG - 350 kcmil

Configuration

Physical Attribute - Number of Screws	2
Number Of Ports	2
Connector Type	Multi Tap

Current

Operating Voltage	600 V
Voltage - Maximum	600 V

Dimensions

Package Height	0.000 in
Dimension - Height mm	64 mm
Dimension - Height inch	2.5 in
Dimension - Height fraction	2.5 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	56 mm
Dimension - Width fraction	2-8/25 in
Dimension - Width mm	59 mm
Dimension - Width inch	2.32 in
Dimension - Length Overall inch	2.22 in

General

Insulation Type	Plastisol
Trade Name	UNITAP™
Material - Hardware	Aluminum

Insulation	Y
Physical Attribute - Screw Type	Allen
Plated	N
Sub Brand	UNITAP
UPC	781810133538
Type	BIT
Hex Key	5/16 in
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810133538
UPC 14 Digit GTIN	00781810133538

Logistics

Pallet Quantity	2160
Carton Quantity	60

Operational

Temperature Rating	90 °C
--------------------	-------

Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)



A Hubbell brand