

BIT600, 1-Side, 2-Cond. Clear Ins., MultiTap

By Burndy
Catalog # [BIT600](#)

Aluminum Multiple Tap Connector, Clear Insulated, 2 Port, 1 Sided Entry, 4 AWG-600 kcmil, Al/Cu Rated



Features

- Type BIT and BITO (Offset) Multi-tap connectors are installed quickly and easily
- Suitable for use on Code conductor
- UL486B Listed, Dual-rated AL9CU.

Application

For Indoor Use Only, Copper Or Stranded Aluminum

Specifications

EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - AL Str Size Range	4 AWG - 600 kcmil
Conductor Size	4 AWG-600 KCMIL
Conductor Type	• AL C Str-Size • CU C Str-Size
Conductor - Copper Str Size Range	4 AWG - 600 kcmil

Configuration

Physical Attribute - Number of Screws	2
Number Of Ports	2
Connector Type	Multi Tap

Current

Operating Voltage	600 V
Voltage - Maximum	600 V

Dimensions

Package Height	0.000 in
Dimension - Height mm	69.9 mm
Dimension - Height inch	2.75 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	69 mm
Dimension - Width fraction	2-19/50 in
Dimension - Width mm	60 mm
Dimension - Width inch	2.38 in
Dimension - Length Overall inch	2.72 in

General

Insulation Type	Plastisol
Trade Name	UNITAP™
Material - Hardware	Aluminum
Insulation	Y
Physical Attribute - Screw Type	Allen
Plated	N
Sub Brand	UNITAP
UPC	781810225257
Type	BIT
Hex Key	3/16
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810225257
UPC 14 Digit GTIN	00781810225257

Logistics

Pallet Quantity	1400
Carton Quantity	50

Operational

Temperature Rating	90°C
--------------------	------

Product Assets

[Catalog \[English\]](#)
[Catalog \[English\]](#)