



BITO250FX, Opp. Side, Flex, 2-Cond. Clear Ins. MultiTap

By Burndy
Catalog # [BITO250FX](#)



Aluminum UNITAP, Tap - Opposite Side Entry, #10-250 Class B & C, #10-3/0 Class G,H,I,K, DLO, 2 PORT

Features

- Type BIT-FX and BITO-FX Multi-tap connectors are quickly and easily installed
- UL486B Listed, Dual rated AL9CUFor stranded copper or stranded aluminum applications

Specifications

Standards - Industry Standards	UL 486A-486B
Met	
Standards - RoHS Compliance	CM
Status	
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper DLO Size	10 str.-3/0 str.
Range	
Conductor Size	10 AWG-250 KCMIL
Conductor - Copper Flex G Size	10 str.-3/0 str.
Range	
Conductor - Copper Flex K Size	10 str.-3/0 str.
Range	
Conductor - AL Str Size Range	10 AWG - 250 kcmil
Conductor Type	• AL C Str-Size • CU C Str-Size • CU C Flex-Size
Conductor - Copper Str Size	10 AWG - 250 kcmil
Range	
Conductor - Copper Flex H Size	10 str.-3/0 str.
Range	
Conductor - Copper Flex I Size	10 str.-3/0 str.
Range	

Configuration

Number Of Ports	2
Connector Type	Multi Tap

Current

Operating Voltage	600 V
Voltage - Maximum	600 V

Dimensions

Package Height	0.000 in
Dimension - Height mm	54.10 mm
Dimension - Height inch	2.13 in
Package Weight	0.000 lb.
Dimension - Width mm	66.82 mm
Dimension - Width inch	2.63 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	52.00 mm
Dimension - Length Overall inch	2.03 in

General

Plated	Y
Color Code	Yellow
Trade Name	UNITAP™
UPC	621945440654
Insulation	Y
Hex Key	5/16 in
Material	Aluminum
Plating Type	Tin Plated
UPC 12 Digit	621945440654
UPC 14 Digit GTIN	00621945440654

Logistics

Pallet Quantity	2700
Carton Quantity	100

Operational

Temperature Rating	135°C
--------------------	-------

Product Assets

[Catalog \[English\]](#)
[Catalog \[English\]](#)