



BITO350, Opp. Side, 2-Cond., Clear Ins. MultiTap

By Burndy
Catalog # [BITO350](#)

Aluminum Multiple Tap Connector, Clear Insulated, 2 Port, 2 Sided Entry, 10 AWG-350 kcmil



Features

- Type BIT and BITO (Offset) Multi-tap connectors are installed quickly and easily
- Suitable for use on Code conductor
- UL486B Listed, Dual-rated AL9CU.

Application

For Indoor Use Only, Copper Or Stranded Aluminum

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - AL Str Size Range	8 str.-350 kcmil
Conductor Size	10 AWG-350 KCMIL
Conductor Type	• AL C Str-Size • CU C Str-Size
Conductor - Copper Str Size Range	8 AWG - 350 kcmil

Configuration

Physical Attribute - Number of Screws	2
Number Of Ports	2
Connector Type	Multi Tap

Current

Operating Voltage	600 V
Voltage - Maximum	600 V

Dimensions

Package Height	0.000 in
Dimension - Height mm	64.00 mm
Dimension - Height inch	2.50 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	56 mm
Dimension - Width mm	76 mm
Dimension - Width inch	3.00 in
Dimension - Length Overall inch	2.22 in

General

Insulation Type	Plastisol
Trade Name	UNITAP™
Material - Hardware	Aluminum
Insulation	Y
Physical Attribute - Screw Type	Allen
Plated	N
Sub Brand	UNITAP
UPC	781810155936
Type	BIT
Hex Key	5/16
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810155936
UPC 14 Digit GTIN	00781810155936

Logistics

Pallet Quantity	3750
Carton Quantity	50

Operational

Temperature Rating	90°C
--------------------	------

Product Assets

[Catalog \[English\]](#)
[Catalog \[English\]](#)



A Hubbell brand