



BITO350FX, Opp. Side, Flex, 2-Cond. Clear Ins. MultiTap

By Burndy
Catalog # [BITO350FX](#)



Aluminum UNITAP, Tap - Opposite Side Entry, #10-350 Class B & C, #10-250 Class G,H,I,K, DLO, 2 PORT

Features

- Type BIT-FX and BITO-FX Multi-tap connectors are quickly and easily installed
- UL486B Listed, Dual rated AL9CUFor stranded copper or stranded aluminum applications

Specifications

Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper DLO Size Range	10 str.- 250 kcmil
Conductor Size	10 AWG-350 KCMIL
Conductor - Copper Flex G Size Range	10 str.- 250 kcmil
Conductor - Copper Flex K Size Range	10 str.- 250 kcmil
Conductor - AL Str Size Range	10 AWG - 350 kcmil
Conductor Type	• AL C Str-Size • CU C Str-Size • CU C Flex-Size
Conductor - Copper Str Size Range	10 AWG - 350 kcmil
Conductor - Copper Flex H Size Range	10 str.- 250 kcmil
Conductor - Copper Flex I Size Range	10 str.- 250 kcmil

Configuration

Number Of Ports	2
Connector Type	Multi Tap

Current

Operating Voltage	600 V
Voltage - Maximum	600 V

Dimensions

Package Height	0.000 in
Dimension - Height mm	63.50 mm
Dimension - Height inch	2.50 in
Package Weight	0.000 lb.
Dimension - Width mm	69.85 mm
Dimension - Width inch	2.75 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	56.39 mm
Dimension - Length Overall inch	2.22 in

General

Plated	Y
Color Code	Red
Trade Name	UNITAP™
UPC	621945440661
Insulation	Y
Hex Key	5/16 in
Material	Aluminum
Plating Type	Tin Plated
UPC 12 Digit	621945440661
UPC 14 Digit GTIN	00621945440661

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1600
Carton Quantity	50

Operational

Temperature Rating	135°C
--------------------	-------

Product Assets

[Catalog \[English\]](#)
[Catalog \[English\]](#)