



# BITO600FX, Opp. Side, Flex, 2-Cond. Clear Ins, MultiTap

By Burndy  
Catalog # [BITO600FX](#)



Aluminum UNITAP, Tap - Opposite Side Entry, #4-600 Class B & C, #4-373 Class G,H,I,K, DLO, 2 PORT

### Features

- Type BIT-FX and BITO-FX Multi-tap connectors are quickly and easily installed
- UL486B Listed, Dual rated AL9CUFor stranded copper or stranded aluminum applications

### Specifications

|                                |              |
|--------------------------------|--------------|
| Standards - Industry Standards | UL 486A-486B |
| Met                            |              |
| Standards - RoHS Compliance    | CM           |
| Status                         |              |
| Industry Standard(s)           | UL 486A-486B |
| UL Listed                      | Yes          |
| Certification - CSA Approved   | Yes          |

### Conductor

|                                |                                                                                                                  |
|--------------------------------|------------------------------------------------------------------------------------------------------------------|
| Conductor - Copper DLO Size    | 4 str.-373 kcmil                                                                                                 |
| Range                          |                                                                                                                  |
| Conductor Size                 | 4 AWG-600 KCMIL                                                                                                  |
| Conductor - Copper Flex G Size | 4 str.-373 kcmil                                                                                                 |
| Range                          |                                                                                                                  |
| Conductor - Copper Flex K Size | 4 str.-373 kcmil                                                                                                 |
| Range                          |                                                                                                                  |
| Conductor - AL Str Size Range  | 4 AWG - 600 kcmil                                                                                                |
| Conductor Type                 | <ul style="list-style-type: none"><li>• AL C Str-Size</li><li>• CU C Str-Size</li><li>• CU C Flex-Size</li></ul> |
| Conductor - Copper Str Size    | 4 AWG - 600 kcmil                                                                                                |
| Range                          |                                                                                                                  |
| Conductor - Copper Flex H Size | 4 str.-373 kcmil                                                                                                 |
| Range                          |                                                                                                                  |
| Conductor - Copper Flex I Size | 4 str.-373 kcmil                                                                                                 |
| Range                          |                                                                                                                  |

### Configuration

|                 |           |
|-----------------|-----------|
| Number Of Ports | 2         |
| Connector Type  | Multi Tap |

### Current

|                   |       |
|-------------------|-------|
| Operating Voltage | 600 V |
| Voltage - Maximum | 600 V |

### Dimensions

|                                 |           |
|---------------------------------|-----------|
| Package Height                  | 0.000 in  |
| Dimension - Height mm           | 69.85 mm  |
| Dimension - Height inch         | 2.75 in   |
| Package Weight                  | 0.000 lb. |
| Dimension - Width mm            | 69.85 mm  |
| Dimension - Width inch          | 2.75 in   |
| Package Length                  | 0.000 in  |
| Package Width                   | 0.000 in  |
| Dimension - L Length Overall mm | 69.85 mm  |
| Dimension - Length Overall inch | 2.75 in   |

### General

|                   |                |
|-------------------|----------------|
| Plated            | Y              |
| Color Code        | Green          |
| Trade Name        | UNITAP™        |
| UPC               | 621945440685   |
| Insulation        | Y              |
| Hex Key           | 3/8 in         |
| Material          | Aluminum       |
| Plating Type      | Tin Plated     |
| UPC 12 Digit      | 621945440685   |
| UPC 14 Digit GTIN | 00621945440685 |

### Logistics

|                       |      |
|-----------------------|------|
| Minimum Pack Quantity | 1    |
| Pallet Quantity       | 1600 |
| Carton Quantity       | 50   |

### Operational

|                    |       |
|--------------------|-------|
| Temperature Rating | 135°C |
|--------------------|-------|

### Product Assets

[Catalog \[English\]](#)  
[Catalog \[English\]](#)