



BSD2050N, Static Discharge Reel, Heavy Duty, Cable Length: 50' (Nylon Covered)

By Burndy
Catalog # BSD2050N

Static Discharge Reels, Heavy Duty, Cable Length: 50 Feet (Nylon Covered)

Features

- 50 foot cable length
- Automatic E-Z PULL Rewinding
- Rugged Steel Construction
- Compact Enclosed Design
- Positive Ratchet Lock with Ratchet On/Off Switch
- Steel Cable Installed
- 100 Amp Universal Jaw-Type GroundingClamp
- Red Baked-on Finish

Application

Used to dissipate static charge build-up developed while filling or dispensing fuel or other combustible liquids from fuel trucks or rail cars

Specifications

EU RoHS Indicator	Contact Manufacturer
Certification - CSA Approved	No

Conductor

Conductor Type	• CU C Solid-Size • CU C Str-Size
Cable Type	Aircraft Steel

Configuration

Physical Attribute - Number of Clamping Elements	1
--	---

Dimensions

Dimension - Height mm	223.5 mm
Dimension - Height inch	8.8 in



Dimension - Width mm	86 mm
Dimension - Width inch	3.40 in
Dimension - L Length Overall mm	219 mm
Cable Length	50 ft
Cable Length Active	600
Dimension - Length Overall inch	8.6 in

Force Related

Tension	Adjustable
---------	------------

General

Plated	N
Sub Brand	REEL
Color - Housing	Red
UPC	781810504475
Type	Static Discharge Reel
Material Type - Outer Shell	Nylon
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810504475
Cable Lock	Y
UPC 14 Digit GTIN	00781810504475

Logistics

Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)