



# BURNDY

**BSD2050Y, Static Discharge Reel, Heavy Duty, Cable Length: 35' plus 15' for Y**

By Burndy

Catalog # [BSD2050Y](#)

Static Discharge Reels, Heavy Duty, Cable Length: 35 Feet Plus 15 FT for Y



## Features

- 35 foot cable length plus 15 foot for Y
- Automatic E-Z PULL Rewinding
- Rugged Steel Construction
- Compact Enclosed Design
- Positive Ratchet Lock with Ratchet On/Off Switch
- Steel Cable Installed
- 100 Amp Universal Jaw-Type Grounding Clamp
- Red Baked-on Finish

## Specifications

Buy America(n) Qualified  
Contact Manufacturer  
Certification - CSA Approved  
No

Conductor

Conductor Type

- CU C Solid-Size
- CU C Str-Size

Cable Type  
Aircraft Steel

Configuration

Physical Attribute - Number of Clamping Elements  
2

Dimensions

Dimension - Height mm  
223.5 mm  
Dimension - Height inch  
8.80 in  
Dimension - Width mm  
86 mm  
Dimension - Width inch  
3.40 in  
Cable Length  
50 ft  
Cable Length Active  
600  
Dimension - Length Overall inch  
8.60 in

Force Related

Tension  
Adjustable

General

Plated  
N  
Color - Housing  
Red  
UPC  
781810504482  
Material  
Copper  
Plating Type  
Unplated  
UPC 12 Digit  
781810504482  
Cable Lock  
Y  
UPC 14 Digit GTIN  
00781810504482

Logistics

Minimum Pack Quantity  
1  
Pallet Quantity  
270  
Carton Quantity  
1

Product Assets

[Catalog.\[English\]](#)



A Hubbell brand  
© 2026 Hubbell Incorporated. All rights reserved  
BRDY-BSD2050Y-SPEC-EN | REV 5/2026