



BSLK2C2A, Streetlight Tap Disconnect Fuse Connector,Y Style

By Burndy
Catalog # [BSLK2C2A](#)

Streetlight Tap, Disconnect Fuse Connector, "Y" Style, #14-2 Cu, #10-2 AL, 600V, 30 AMP

Features

- Wire Compatibility: Supports 10-2 AWG aluminum and 14-2 AWG copper conductors
- Dual-Rated Body: Aluminum housing rated for both aluminum and copper wires
- Configuration Options: Available in In-Line and "Y" styles for flexible installation
- Fuse Compatibility: Supplied with dummy fuse, compatible with UL248, Part 14 fuse classes
- Environmental Resistance: EPDM rubber housing provides protection against moisture and debris
- Electrical Ratings: 600V, 30 AMP capacity
- Breakaway Design: Helps reduce wire damage if fixture is displaced

Specifications

Buy America(n) Qualified	TAA Compliant (All status valid till December 2026)
--------------------------	---

Conductor

Conductor Range	• #14-2 Cu • #10-2 AL
-----------------	---

Current

Amperage Rating	600V, 30 AMP
-----------------	--------------



Dimensions

Height	1.85 in
Width	1.85 in
Package Height	0.000 in
Length	7.65 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimensions	7.65 in x 1.85 in x 1.85 in

Force Related

Installation Torque Recommended in-lb	Cu 14 - 35 in-lb, Cu 10-12 - 40 in-lb, Cu 8-2 - 100 in-lb, AL 10-8 - 45 in-lb, AL 6 - 65 in-lb, AL 4-2 - 100 in-lb
---------------------------------------	--

General

UPC	621945717589
-----	--------------

Logistics

Carton Quantity	1
-----------------	---

Product Assets

[Catalog Page \[English\]](#)
[Installation Manual \[English\]](#)