



BWB680IG, In-Ground Pool Water Bonding Kit

By Burndy
Catalog # [BWB680IG](#)

Pool Water Bonding Kit, In-Ground; 3/16" Stud, includes: 1 bonding plate (stainless steel), 1 connector, 1 rubber sealing washer, 2 flat washers, 2 lock washers

Features

- Easy Installation
- Mounting Hardware Included
- UL Listed
- Placed out of the way on the side wall of the skimmer below basket

Application

For In Ground Pool

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	No



Dimensions

Package Height	4.000 in
Package Weight	3.060 lb.
Package Length	8.250 in
Package Width	6.000 in

General

Mounting Type	Wall Mount
UPC	781810498682
Type	Pool Water Bonding Kit
Construction Material - Main	Non-corrosive stainless steel
UPC 12 Digit	781810498682
UPC 14 Digit GTIN	00781810498682

Logistics

Pallet Quantity	3000
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)