

C11CSH2, Bronze Clamp with Copper Strap, Cable to Water Pipe

By Burndy
Catalog # [C11CSH2](#)

Cast Bronze Clamp with Copper Strap, Cable to Water Pipe, 4/0 AWG (Str.), 1/2"- 1" Water Pipe, 3/4" hub



Features

- For grounding rigid conduit systems, straps helps protect conduit system from water system vibrations
- Zinc-plated screw, Strap ETP Copper

Application

For Grounding Rigid Conduit Systems

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	CM
Status	
Certification - UL Listed Direct	No
Burial	
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Pipe EMT Size Range	1/2 in-1 in
Conductor - Pipe EMT Size	• 1/2 in • 3/4 in • 1 in
Conductor - Copper Str Size	8 STR - 4 STR
Conductor - Copper Solid Size	8 SOL - 4 SOL
Conductor - Armored Cable Size	N
Conductor - Copper Solid Size Range	8 SOL - 4 SOL
Conductor - Copper Str Size Range	8 AWG - 4 AWG

Dimensions

Dimension - Pad Width inch	1.50 in
----------------------------	---------

Package Height	3.400 in
Dimension - Height mm	44.5 mm
Dimension - Height inch	1.75 in
Package Weight	2.170 lb.
Package Length	9.000 in
Package Width	6.500 in
Dimension - L Length Overall mm	216 mm
Dimension - Width mm	32 mm
Dimension - Width inch	1.25 in
Dimension - D inch	6.12 in
Dimension - Length Overall inch	8.50 in

General

Product Family	Grounding and Bonding Connectors>Copper Mechanical Grounding Connectors>Cable(s) to Ground Rod/Pipe/Tube (GAR/GD/GK)>LC Water Pipe Ground Clamps
Material - Hardware	Zinc Plated Steel
Plated	No
Sub Brand	CLAMP
Product Type	Mechanical
UPC	781810142486
Type	WaterPipe Gounding Connectors
Material	Bronze Alloy
Plating Type	Zinc
UPC 12 Digit	781810142486
UPC 14 Digit GTIN	00781810142486

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1500
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)